

AGILA TWIN

2970PJP050P30-11 TNL

EAN 4031582333541



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	70 mm
Overall weight	0.54 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	25 mm
Swivel radius	50 mm
Swivel interference	100 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

AGILA TWIN

2970PJP050P30-11 TNL

EAN 4031582333541



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

