

LUMINA

A520PJI050B10-11X20/10D45 9011/7042

EAN 4031582317152
Order number 00074223



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12529 - Swivel Chairs Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	61 mm
Overall width	54 mm
Overall weight	0.105 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Traffic grey A (RAL7042)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	8 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	45 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

PRODUCT INFORMATION

LUMINA

A520PJI050B10-11X20/10D45 9011/7042

EAN 4031582317152
Order number 00074223



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

