

LUMINA

AA20PJI050L51-8 9011/9011/7042

EAN 4031582317473



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	56 mm
Overall width	55 mm
Overall weight	0.07 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Traffic grey A (RAL7042)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	10 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	8 mm

LUMINA

AA20PJ1050L51-8 9011/9011/7042

EAN 4031582317473

Order number 00071465
Product Drawings



BETTER MOBILITY. BETTER LIFE.

