

ALPHA

8476UFX160P67 OH200 brake-asm

EAN 4031582380545



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Alpha
Type	Swivel castor with central, total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall Height	200 mm
Overall width	99 mm
Overall weight	1.88 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Stainless steel
Offset	55 mm
Swivel radius	143.5 mm
Swivel interference	287 mm
Dome diameter	96 mm

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

FITTING

Fitting type	Plate with central locking
Plate length	176 mm
Plate width	112 mm
Plate hole length (Maximum)	77.5 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	13 mm

ALPHA

8476UFX160P67 OH200 brake-asm

EAN 4031582380545

Order number 00064659

Product Drawings



BETTER MOBILITY. BETTER LIFE.

