

DURATECH

MOP 150X50-Ø30 HL60

EAN 4031582320022
Order number 00801260



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	150 mm
Tread width	50 mm
Axle hole diameter	30 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D
Bearing type	6306

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2520 kg
Load capacity at 6 km/h	2100 kg
Load capacity Static	4200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	1.446 kg

DURATECH

MOP 150X50-Ø30 HL60

EAN 4031582320022
Order number 00801260



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

