

# DELTA TWIN

9940ETP065P41-100x100

EAN 4031582501162

Order number 00800241



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Delta twin                    |
| Type                        | Swivel caster                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 881.85 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 1763.7 lb                     |
| Temperature range (Minimum) | -22 °F                        |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 4.39 in                       |
| Overall width               | 3.62 in                       |
| Overall weight              | 4.26 lb                       |

## HOUSING

|                     |                                  |
|---------------------|----------------------------------|
| Housing Material    | Cast iron, or iron forged, heavy |
| Fork shape          | Twin wheel housing               |
| Swivel bearing      | Precision ball bearing           |
| Housing Color       | Transparent coating              |
| Offset              | 0.98 in                          |
| Swivel radius       | 2.44 in                          |
| Swivel interference | 4.88 in                          |
| Dome diameter       | 2.87 in                          |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Steel, iron            |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 2.56 in                |
| Tread width           | 1.18 in                |
| Body width            | 1.18 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 3.94 in      |
| Plate width                 | 3.94 in      |
| Plate hole length (Minimum) | 2.48 in      |
| Plate hole length (Maximum) | 3.07 in      |
| Plate hole width (Minimum)  | 2.48 in      |
| Plate hole width (Maximum)  | 3.07 in      |
| Plate hole diameter         | 0.41 in      |

# DELTA TWIN

9940ETP065P41-100x100

EAN 4031582501162

Order number 00800241

Product Drawings



BETTER MOBILITY. BETTER LIFE.

