

AGILA TWIN

2970UOO075P50 TFR

EAN 4031582394252



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	102 mm
Overall weight	0.517 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	50 mm
Tread width	44 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31.4 mm
Swivel radius	56.4 mm
Swivel interference	112.8 mm

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	56 mm
Plate hole length (Maximum)	61.5 mm
Plate hole width (Minimum)	46.5 mm
Plate hole width (Maximum)	51.5 mm

PRODUCT INFORMATION

AGILA TWIN

2970UOO075P50 TFR

EAN 4031582394252



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

