

# ALPHA

3472PXU160P63

EAN 4031582304930



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	135 kg
Load capacity Static	270 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	200 mm
Overall weight	2.329 kg

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, biosourced, injected, electric-conductive
Bearing	Plain bearing with synthetic spacer Tube
Axle	Screwed with nut
Diameter	160 mm
Tread width	40 mm
Hardness of tread (A)	85 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ALPHA

3472PXU160P63

EAN 4031582304930



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

