

FOOTMASTER

FOOT MASTER GDR- 80-F-NYN

EAN 4031582413311



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ○ ○ ○ ○ ○ |
| Movement Noise | ○ ○ ○ ○ ○ |
| Attrition | ○ ○ ○ ○ ○ |
| Corrosion Resistance | ○ ○ ○ ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------|
| Product Name | Footmaster |
| Type | Swivel castor |
| Load capacity at 3 km/h | 500 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 90 °C |
| Overall Height | 102 mm |
| Overall width | 86 mm |
| Overall weight | 2 kg |

HOUSING

| | |
|---------------------|---------|
| Housing Color | White |
| Offset | 46 mm |
| Swivel radius | 77.5 mm |
| Swivel interference | 155 mm |
| Dome diameter | 86 mm |

WHEEL

| | |
|-------------|------------------------|
| Bearing | Roller bearing, damped |
| Wheel Color | Black |
| Diameter | 63 mm |
| Tread width | 30 mm |
| Body width | 30 mm |

FITTING

| | |
|-----------------------------|-------|
| Plate length | 90 mm |
| Plate width | 90 mm |
| Plate hole length (Maximum) | 70 mm |
| Plate hole width (Maximum) | 70 mm |
| Plate hole diameter | 9 mm |

FOOTMASTER

FOOT MASTER GDR- 80-F-NYN

EAN 4031582413311

Order number 00062082
Product Drawings



BETTER MOBILITY. BETTER LIFE.

