

# AGILA

2470DIK125R07-Ø21,5-24

EAN 4031582328325  
Order number 00035649



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	6.42 in
Overall weight	2.57 lb

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	4.07 in
Swivel interference	8.15 in

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.85 in
Expander fitting (Maximum)	0.94 in
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470DIK125R07-Ø21,5-24

EAN 4031582328325  
Order number 00035649



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

