

# AGILA STAINLESS

7470PJO050P40

EAN 4031582350968



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila stainless           |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 40 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | Yes                       |
| Load capacity Static        | 80 kg                     |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 69 mm                     |
| Overall width               | 43 mm                     |
| Overall weight              | 0.18 kg                   |

## HOUSING

|                     |                         |
|---------------------|-------------------------|
| Housing Material    | Stainless steel, medium |
| Fork shape          | Broad                   |
| Swivel Bearing      | Two ball races          |
| Housing Color       | Stainless steel         |
| Offset              | 24 mm                   |
| Swivel radius       | 49 mm                   |
| Swivel interference | 98 mm                   |
| Dome diameter       | 41 mm                   |

## WHEEL

|                       |                       |
|-----------------------|-----------------------|
| Body material         | Polypropylene         |
| Tread Material Mix    | Thermoplastic rubber  |
| Bearing               | Plain bearing         |
| Wheel Color           | Silver grey (RAL7001) |
| Threadguards          | Without threadguard   |
| Diameter              | 50 mm                 |
| Tread width           | 19 mm                 |
| Body width            | 19 mm                 |
| Hardness of tread (A) | 87 Shore A            |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 60 mm        |
| Plate width                 | 60 mm        |
| Plate hole length (Minimum) | 38 mm        |
| Plate hole length (Maximum) | 48 mm        |
| Plate hole width (Minimum)  | 38 mm        |
| Plate hole width (Maximum)  | 48 mm        |
| Plate hole diameter         | 6.3 mm       |

# AGILA STAINLESS

7470PJO050P40

EAN 4031582350968

Order number 00036673

Product Drawings



BETTER MOBILITY. BETTER LIFE.

