

DELTA TWIN

9948ITP200P63 SOFT CV

EAN 4031582365931
Order number 00837763



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Delta twin |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 750 kg |
| Load capacity at 6 km/h | 600 kg |
| Load capacity Static | 1500 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 250 mm |
| Overall width | 157 mm |
| Overall weight | 5.22 kg |

WHEEL

| | |
|-----------------------|--------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Traffic grey A (RAL7042) |
| Threadguards | Without threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Body width | 50 mm |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------|---------------------|
| Material | Iron forged, heavy |
| Fork shape | Twin wheel housing |
| Colour | Transparent coating |
| Dome diameter | 136 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 137 mm |
| Plate width | 137 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 105 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

DELTA TWIN

9948ITP200P63 SOFT CV

EAN 4031582365931
Order number 00837763



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

