

STYLEA

5920UOI065P41-38X38/10 ALU

EAN 4031582410075



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	78 mm
Overall width	46 mm
Overall weight	0.092 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	7 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	53 mm
Swivel interference	106 mm

FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm
Plate hole length (Maximum)	27 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	5 mm