

OMIKRON TWIN

9950STP500P68 RADBREITE 100

EAN 4031582428964



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Swivel castor
Load capacity at 1.8 mph	22046.2 lb
Load capacity at 2.5 mph	22046.2 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	24.02 in
Overall weight	288.53 lb

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	19.69 in
Tread width	3.94 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	5.12 in
Swivel radius	14.96 in
Swivel interference	29.92 in

FITTING

Fitting type	Rectangular plate
Plate length	10.63 in
Plate width	9.84 in
Plate hole length (Maximum)	9.06 in
Plate hole width (Maximum)	8.27 in
Plate hole diameter	0.67 in

OMIKRON TWIN

9950STP500P68 RADBREITE 100

EAN 4031582428964



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

