

ZETA REVERSE

468BITP250P63 180° CONV

EAN 4031582480924



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta reverse
Housing type	Swivel castor with total lock and spring loaded directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	290 mm
Overall weight	3.928 kg

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel interference	360 mm

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA REVERSE

468BITP250P63 180° CONV

EAN 4031582480924



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

