

GALEA

5071PIP125P30-12

EAN 4031582354232



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Galea
Housing type	Swivel castor with directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	162 mm
Overall weight	0.552 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Offset	40 mm
Swivel interference	205 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	12 mm

GALEA

5071PIP125P30-12

EAN 4031582354232



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

