

ICS

5328XSX125P51 7001 INOX 7001

EAN 4031582310344
Order number 00030787



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------|
| Roll performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●●● |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | ICS |
| Type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric conductive | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 166 mm |
| Overall width | 52 mm |
| Overall weight | 0.765 kg |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing, sealed |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Integrated threadguard |
| Diameter | 125 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 91 Shore A |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------|-------------------------------|
| Material fork | Polyamide |
| Fork shape | Slim |
| Colour | Silver grey (similar RAL7001) |
| Dome diameter | 52 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 95 mm |
| Plate width | 70 mm |
| Plate hole length (Maximum) | 50 mm |
| Plate hole width (Maximum) | 75 mm |
| Plate hole diameter | 11 mm |



IF
Design
Award

ICS



5328XSX125P51 7001 INOX 7001

EAN 4031582310344
Order number 00030787



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



IF
Design
Award