PRODUCT INFORMATION

LEVINA

5377XSP100R05-28x45

EAN 4031582360295



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●●○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Levina
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	137 mm

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Swivel Bearing	Two ball races
Offset	36 mm
Swivel radius	98 mm
Swivel interference	196 mm

WHEEL

Body material	Polyamide, electric conductive
Tread Material Mix	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm

Universal Design Award

Deutscher Designer Club

© Copyright 2026 TENTE International GmbH


LEVINA


5377XSP100R05-28x45

EAN 4031582360295

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH