

# ANIKA

5925PJI065L51-10 DOM18

EAN 4031582433425



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Anika
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	67 mm
Overall width	39.5 mm
Overall weight	0.084 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	11 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	76 mm
Swivel interference	152 mm
Dome diameter	18 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



PRODUCT INFORMATION

# ANIKA

5925PJI065L51-10 DOM18

EAN 4031582433425



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Interzum  
Award