

# OMIKRON TWIN

9950FTP250P68

EAN 4031582316810  
Order number 00801114



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	5000 kg
Load capacity at 6 km/h	3600 kg
Load capacity Static	7500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	365 mm
Overall width	272 mm
Overall weight	54.457 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Transparent coating
Offset	70 mm
Swivel radius	210.5 mm
Swivel interference	421 mm
Lubrication nipple	✓
Dome diameter	250.5 mm

## FITTING

Fitting type	Extra large rectangular heavy-duty plate
Plate length	270 mm
Plate width	250 mm
Plate hole length (Maximum)	210 mm
Plate hole width (Maximum)	230 mm
Plate hole diameter	17 mm

# OMIKRON TWIN

9950FTP250P68

EAN 4031582316810  
Order number 00801114



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

9950...250P68

