

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor with total lock
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Overall height	99 mm

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31 mm
Swivel interference	198 mm

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

