

# FOOTMASTER

FOOT MASTER GD- 60-F-NYN

EAN 4031582413205



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	280 kg
Electric Conductive	No
Stainless	No
Load capacity Static	280 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	82 mm
Overall width	70 mm
Overall weight	0.7 kg

## HOUSING

Housing Color	White
Offset	36 mm
Swivel radius	61 mm
Swivel interference	122 mm
Dome diameter	70 mm

## WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	50 mm
Tread width	25 mm
Body width	25 mm

## FITTING

Plate length	73 mm
Plate width	73 mm
Plate hole length (Maximum)	58 mm
Plate hole width (Maximum)	58 mm
Plate hole diameter	7 mm

# FOOTMASTER

FOOT MASTER GD- 60-F-NYN

EAN 4031582413205

Order number 00062068  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

