

# GALEA STAINLESS

5081PJM125P30-12

EAN 4031582383478



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

## CORE ATTRIBUTES

Product name	Galea stainless
Type	Swivel castor with directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Stainless	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	162 mm
Overall width	66 mm
Overall weight	0.541 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing, stainless
Threadguards	With threadguard
Diameter	125 mm
Tread width	30 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races, reinforced or stainless
Offset	40 mm
Swivel radius	129 mm
Swivel interference	258 mm
Dome diameter	59 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	12 mm

# GALEA STAINLESS

5081PJM125P30-12

EAN 4031582383478



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

