

# STYLEA

5920UJI065L51-10 DOM23 RAL9006



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	68 mm
Overall width	43 mm
Overall weight	0.088 kg

## WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	White aluminium (similar RAL9006)
Threadguards	Without threadguard
Diameter	65 mm
Tread width	8 mm
Body width	8 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	White aluminium (similar RAL9006)
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	23 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

# STYLEA

5920UJI065L51-10 DOM23 RAL9006



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

