

## S70-10X15 / 10 DRILLED STEM

EAN 4031582411904



Image may differ from the original product

### PERFORMANCE

Corrosion resistance ● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Overall height	6 mm
Overall weight	0.025 kg

### FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm