

KAPPA LOAD

9658FCP200P63

EAN 4031582451931



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3086.47 lb
Load capacity at 3.7 mph	2645.54 lb
Load capacity Static	6172.94 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in
Overall weight	10.11 lb

WHEEL

Body material	Casting
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

KAPPA LOAD

9658FCP200P63

EAN 4031582451931



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

