

AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 50 kg                     |
| Electric Conductive         | Yes                       |
| Stainless                   | No                        |
| Load capacity Static        | 100 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 69 mm                     |
| Overall weight              | 0.1 kg                    |

HOUSING

|                  |                     |
|------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape       | Broad               |
| Housing Color    | Blue passivated     |

WHEEL

|                       |                                           |
|-----------------------|-------------------------------------------|
| Body material         | Polypropylene, electric conductive        |
| Tread Material Mix    | Thermoplastic rubber, electric-conductive |
| Bearing               | Plain bearing                             |
| Threadguards          | Without threadguard                       |
| Diameter              | 50 mm                                     |
| Tread width           | 19 mm                                     |
| Hardness of tread (A) | 87 Shore A                                |

FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 55 mm        |
| Plate width                 | 55 mm        |
| Plate hole length (Minimum) | 38.5 mm      |
| Plate hole length (Maximum) | 44 mm        |
| Plate hole width (Minimum)  | 38.5 mm      |
| Plate hole width (Maximum)  | 44 mm        |
| Plate hole diameter         | 6.3 mm       |

# AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

