

AGILA STAINLESS

7477PJO150P51

EAN 4031582350500



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel caster with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	7.2 in
Overall weight	2.1 lb

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Stainless steel
Offset	1.42 in
Swivel interference	10.31 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	5.91 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.74 in
Plate width	2.76 in
Plate hole length (Maximum)	2.95 in
Plate hole width (Maximum)	1.97 in
Plate hole diameter	0.43 in

AGILA STAINLESS

7477PJO150P51

EAN 4031582350500



BETTER MOBILITY. BETTER LIFE.

Product Drawings

