

LINEA LIGHT

5925PJI075S70-10X15/10 SCAN RAL9002

EAN 4031582420548



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Load capacity Static	132.28 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.13 in
Overall width	2.17 in
Overall weight	0.41 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.59 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	0.91 in
Swivel radius	3.23 in
Swivel interference	6.46 in
Thread diameter	0 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in



LINEA LIGHT

5925PJI075S70-10X15/10 SCAN RAL9002

EAN 4031582420548



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

