

LUMINA

6A20POI050L51-10 ZAMAK/9011

EAN 4031582335774
Order number 00079239



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	56 mm
Overall width	55 mm
Overall weight	0.091 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Body width	7 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Offset	20 mm
Swivel radius	51 mm
Swivel interference	102 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

PRODUCT INFORMATION

LUMINA

6A20POI050L51-10 ZAMAK/9011

EAN 4031582335774
Order number 00079239



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

