

NOVATECH

FTP 140x60-Ø20 HL68 cv R190

EAN 4031582329421



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE


Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	840 kg
Load capacity at 6 km/h	700 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1400 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	2.76 kg

WHEEL

Tread profile	convex
Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	140 mm
Tread width	60 mm
Axle Hole Diameter	20 mm
Hub Length	68 mm
Body width	60 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6304
Suitable for	bt




PRODUCT INFORMATION

NOVATECH

FTP 140x60-020 H268 cv R190

EAN 4031582389421

Order number 10832269



BETTER MOBILITY. BETTER LIFE.