

OMIKRON TWIN

9958FTP200P65

EAN 4031582316964
Order number 00801882



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Fixed castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 2.5 mph	5511.55 lb
Load capacity at 3.7 mph	4409.24 lb
Load capacity Static	8267.33 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	10.83 in
Overall width	6.06 in
Overall weight	34.76 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Color	Transparent coating
	✓
Dome diameter	6.3 in

FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	4.72 in
Plate hole width (Maximum)	6.3 in
Plate hole diameter	0.59 in

OMIKRON TWIN

9958FTP200P65

EAN 4031582316964
Order number 00801882



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

