

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	50 °C
Overall Height	48 mm
Overall weight	0.06 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular
Swivel radius	32 mm

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Solid rubber, non-marking
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	38 mm
Tread width	15 mm
Hardness of tread (A)	75 Shore A

FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	25 mm
Plate hole length (Maximum)	45 mm
Plate hole width (Maximum)	45 mm
Plate hole diameter	6 mm

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.

Product Drawings

