

KAPPA

9680SEP160P63 CL67

EAN 4031582364644
Order number 00838212



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Kappa
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	450 kg
Load capacity Static	900 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	205 mm
Overall width	110 mm
Overall weight	4.056 kg

WHEEL

Body material	Sheet steel, heavy
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	67 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	58 mm
Swivel radius	140 mm
Swivel interference	280 mm
Lubrication nipple	✓
Dome diameter	111 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9680SEP160P63 CL67

EAN 4031582364644
Order number 00838212



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

