

INTEGRAL TWIN TORSION

3946UAC125R36-32S30 R9002 4xM6 OP

EAN 4031582382556



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Integral twin torsion
Type	Swivel castor with central, total lock
Standard	EN12531 - Hospital Bed Castors
Load capacity at 3 km/h	125 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	375 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall Height	150 mm
Overall width	62 mm
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Twin wheel housing
Swivel Bearing	Precision ball bearing
Housing Color	Blue passivated
Offset	37.5 mm
Swivel radius	100 mm
Swivel interference	200 mm

WHEEL

Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	125 mm
Tread width	12 mm
Hardness of tread (D)	40 Shore D

FITTING

Brake cam	hex cam
Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	32 mm
Bolt length	51 mm
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.



German
Design
Award



Red Dot
Design
Award