

KAPPA

9680TOO250P63

EAN 4031582315288
Order number 00804549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ○ ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Kappa |
| Housing type | Swivel castor |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 1200 kg |
| Load capacity at 6 km/h | 1000 kg |
| Load capacity Static | 2400 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 305 mm |
| Overall weight | 4.875 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 250 mm |
| Tread width | 50 mm |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|---|
| Material fork | Iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Offset | 61 mm |
| Swivel radius | 186 mm |
| Swivel interference | 372 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 135 mm |
| Plate width | 110 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 11 mm |

KAPPA

9680TOO250P63

EAN 4031582315288
Order number 00804549



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

