

GALEA

5070PIO100P30-10

EAN 4031582362343



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Galea |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 132.28 lb |
| Load capacity Static | 264.55 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.47 in |
| Overall weight | 0.1 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Two ball races |
| Offset | 1.57 in |
| Swivel radius | 3.54 in |
| Swivel interference | 7.09 in |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.39 in |

GALEA

5070PIO100P30-10

EAN 4031582362343



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

