

# KAPPA

9688IEP300P63 CL67

EAN 4031582348651  
Order number 00838187



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Kappa                         |
| Housing type                | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 600 kg                        |
| Load capacity at 6 km/h     | 480 kg                        |
| Load capacity Static        | 1200 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |
| Overall height              | 355 mm                        |
| Overall width               | 98 mm                         |
| Overall weight              | 6.343 kg                      |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Body material         | Aluminium                       |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Precision ball bearing          |
| Axle                  | Screwed with nut                |
| Wheel color           | Jet black (similar RAL9005)     |
| Threadguards          | Without threadguard             |
| Diameter              | 300 mm                          |
| Tread width           | 55 mm                           |
| Body width            | 55 mm                           |
| Hardness of tread (A) | 68 Shore A                      |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material      | Iron forged, heavy |
| Fork shape    | Broad, reinforced  |
| Colour        | Blue passivated    |
| Dome diameter | 96 mm              |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 135 mm            |
| Plate width                 | 110 mm            |
| Plate hole length (Minimum) | 75 mm             |
| Plate hole length (Maximum) | 80 mm             |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 105 mm            |
| Plate hole diameter         | 11 mm             |

# KAPPA

9688IEP300P63 CL67

EAN 4031582348651  
Order number 00838187



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

