

KAPPA

9681TOP125P63 CL67

EAN 4031582315691
Order number 00830616



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Kappa |
| Type | Swivel castor with directional lock |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 1851.88 lb |
| Load capacity at 3.7 mph | 1543.23 lb |
| Load capacity Static | 3086.47 lb |
| Temperature range (Minimum) | -22 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.69 in |
| Overall width | 4.33 in |
| Overall weight | 8.59 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 4.92 in |
| Tread width | 1.97 in |
| Body width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|---|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Color | Blue passivated |
| Offset | 1.89 in |
| Swivel radius | 4.43 in |
| Swivel interference | 8.86 in |
| | ✓ |
| Dome diameter | 4.37 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.31 in |
| Plate width | 4.33 in |
| Plate hole length (Minimum) | 2.95 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.43 in |

KAPPA

9681TOP125P63 CL67

EAN 4031582315691
Order number 00830616



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

