

STYLEA

5925YGI065S70-M10X15 DOM23

EAN 4031582438765



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stylea
Type	Accessory
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric conductive	✓
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	74 mm
Overall width	42 mm
Overall weight	0.14 kg

WHEEL

Axle	Riveted
Diameter	65 mm
Tread width	7 mm
Hardness of tread (A)	87 Shore A

FITTING

Stem diameter	10 mm
Stem length	15 mm