

# AGILA TWIN

2970POO075P30-11

EAN 4031582429541



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	60 °C
Overall height	99 mm
Overall weight	0.184 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31.4 mm
Swivel radius	68.9 mm
Swivel interference	137.8 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# AGILA TWIN

2970POO075P30-11

EAN 4031582429541



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

