

# AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

## CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with total lock
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Overall height	99 mm

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31 mm
Swivel interference	198 mm

# AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

