

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Body material         | Polyamide                       |
| Tread hardness        | soft                            |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Roller bearing                  |
| Wheel color           | Silver grey (RAL7001)           |
| Threadguards          | Without threadguard             |
| Diameter              | 100 mm                          |
| Tread width           | 34 mm                           |
| Axle hole diameter    | 12 mm                           |
| Hub length            | 44.4 mm                         |
| Body width            | 34 mm                           |
| Hardness of tread (A) | 63 Shore A                      |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 160 kg                        |
| Load capacity Static        | 320 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.245 kg                      |

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

