

# KAPPA

9680IFP125P63 CL67

EAN 4031582366105  
Order number 00827736



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Kappa
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	170 mm
Overall width	110 mm
Overall weight	3.688 kg

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Grey / non marking
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	48 mm
Swivel radius	112.5 mm
Swivel interference	225 mm
Lubrication nipple	✓
Dome diameter	111 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# KAPPA

9680IFP125P63 CL67

EAN 4031582366105  
Order number 00827736



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

