

# AGILA CARE US

2441JFX125R05-28 KRAFTABHÄNGIG

EAN 4031582300451



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila care US
Housing type	Swivel castor with directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Electric conductive	✓
Load capacity Static	300 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	170 mm
Overall weight	1.561 kg

## WHEEL

Body material	Zinc die-cast
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	75 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Offset	43 mm
Swivel interference	211 mm

## FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm

# AGILA CARE US

2441JFX125R05-28 KRAFTABHÄNGIG

EAN 4031582300451



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

