

# AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.9 in
Overall weight	1.19 lb

## WHEEL

Body material	Polypropylene
	soft
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	75 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	1.24 in
Swivel radius	2.71 in
Swivel interference	5.43 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.39 in

# AGILA TWIN

2970PIP075P30-10

EAN 4031582362282



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

