

# KAPPA

9680FTP100P63 CL67

EAN 4031582314977  
Order number 00802020



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	450 kg
Load capacity Static	900 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	145 mm
Overall width	110 mm
Overall weight	4.449 kg

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	41 mm
Swivel radius	95 mm
Swivel interference	190 mm
Dome diameter	111 mm

## FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# KAPPA

9680FTP100P63 CL67

EAN 4031582314977  
Order number 00802020



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

