

# KAPPA

9688FTP250P65

EAN 4031582316322



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2040 kg
Load capacity at 6 km/h	1700 kg
Load capacity Static	4080 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	305 mm
Overall weight	18.838 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced

## FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	15 mm

# KAPPA

9688FTP250P65

EAN 4031582316322



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

