

COMPACTA

2198UOI030P60-45X20

EAN 4031582030068
Order number 00021134



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Load capacity Static	60 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	34 mm
Overall width	20 mm
Overall weight	0.031 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	30 mm
Tread width	15 mm
Body width	15 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Angular
Colour	Blue passivated
Dome diameter	20 mm

FITTING

Fitting type	Rectangular plate
Plate length	45 mm
Plate width	20 mm
Plate hole length (Maximum)	35 mm
Plate hole width (Maximum)	35 mm
Plate hole diameter	5.5 mm

COMPACTA

2198UOI030P60-45X20

EAN 4031582030068
Order number 00021134



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

