

ICS

5320XSX125S70-10X17 ~7001

EAN 4031582309867



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	ICS
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric conductive	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	162 mm
Overall width	52 mm
Overall weight	0.569 kg

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel color	Silver grey (RAL7001)
Threadguards	Integrated threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Slim
Swivel bearing	Stem, swiveling
Colour	Silver grey (similar RAL7001)
Offset	37 mm
Swivel radius	99.5 mm
Swivel interference	199 mm
Dome diameter	52 mm
Thread diameter	0 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	17 mm



IF
Design
Award

TECHNICAL DRAWINGS

